

# Model KMF 720 | Constant climate chambers with expanded temperature / humidity range

The BINDER KMF ensures absolutely constant test conditions throughout the testing area. A big advantage of this constant climate chamber is its low space requirement and flexibility in terms of water supply. The wide temperature and humidity range make this constant climate chamber ideally suited for stress testing series.

### BENEFITS

- Safe thanks to climatic homogeneity that far exceeds the accuracy required by ICH guidelines as well as THB (85/85), even with a fully loaded unit.
- Reliable thanks to failsafe operation without compromise. The interior and Longlife evaporator plate are made entirely from stainless steel.
- · Smart, as a wide range of accessories makes it highly compatible for adaptation to specific customer requirements.
- Economical thanks to maximum effective volume which allows for 30% larger load compared to the competition.



Model 720

### **MAIN FEATURES**

- Temperature range: -10 °C to +100 °C
- Humidity range: 10 % RH to 98 % RH
- APT.line<sup>™</sup> preheating chamber technology
- Humidity regulation with capacitive humidity sensor and vapor humidification
- Inner chamber made of stainless steel
- BINDER Multi Management Software APT-COM™ Basic Edition
- Intuitive touchscreen controller with time-segment and real-time programming
- Internal data logger, measured values can be read out in open format via USB
- Unit self-test for comprehensive status analysis

- Tight-sealing inner door made of safety glass (ESG)
- Avoidance of glass corrosion by special TIMELESS coating
- 1 stainless steel rack
- Access port with silicone plug, 30 mm, left
- Class 3.1 independent temperature safety device (DIN 12880) with visual and audible temperature alarm
- Computer interface: Ethernet
- Door heating

### **ORDERING INFORMATION**

Interior volume [L]	Voltage	Option model	Version	ArtNo.
	200230 V 1~ ph 50/60 Hz	Standard	KMF720-230V	9020-0345
700	200240 V 1~ ph 50/60 Hz	Standard	KMF720-240V	9020-0346






## **TECHNICAL DATA**

Description	KMF720-230V <sup>1</sup>	KMF720-240V <sup>1</sup>
Article Number	9020-0345	9020-0346
Performance Data Temperature		
Temperature range [°C]	-10100	-10100
Average heating-up rate according to IEC 60068-3-5 [K/min]	0.7	0.7
Average cooling down time according to IEC 60068-3-5 [K/min]	0.4	0.4
Max. heat compensation at 25 °C [W]	450	450
Performance Data Climate		
Temperature range [°C]	1090	1090
Temperature variation depending on setpoint [± K]	0.11	0.11
Temperature fluctuation depending on setpoint [± K]	0.10.5	0.10.5
Humidity range	1098	1098
Humidity fluctuation depending on setpoint	≤2 ± % RH	≤2 ± % RH
Electrical data		
Rated Voltage [V]	200230	200240
Power frequency [Hz]	50/60	50/60
Nominal power [kW]	3.1	3.1
Unit fuse [A]	16	16
Phase (Nominal voltage)	1~	1~
Measures		
Interior volume [L]	700	700
Net weight of the unit (empty) [kg]	306	306
Permitted load [kg]	150	150
Load per rack [kg]	45	45
Wall clearance back [mm]	100	100
Wall clearance sidewise [mm]	100	100
Internal Dimensions		
Width [mm]	973	973
Height [mm]	1250	1250
Depth [mm]	576	576
Doors		
Inner doors	2	2
Unit doors	2	2
Housing dimensions not incl. fittings and connections		
Width net [mm]	1250	1250
Height net [mm]	1925	1925
Depth net [mm]	890	890
Environment-specific data		
Energy consumption at 85 °C and 85 % RH [Wh/h]	900	900
Sound-pressure level [dB(A)]	56	56
Fixtures		
Number of shelves (std./max.)	1/15	1/15


1 All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.



# DIMENSIONS incl. fittings and connections [mm]







ICH Long term stability testing
Accelerated stability testing
ICH Stress testing
Industrial THB testing (85/85)

A: Guaranteed condensation-free range B: Time-limited operation (max. 24 hours) C: Condensation in the inner chamber may be possible

Climate chart

### **OPTIONS**

Designation	Description	*	ArtNo.
	left		
	30 mm	01	8012-1446
	50 mm	01	8012-1476
	100 mm	01	8012-1342
Access port with silicone plug	right		
	30 mm	01	8012-1440
	50 mm	01	8012-1470
	100 mm	01	8012-1339
	top		
	30 mm	01	8012-1452
	50 mm	01	8012-1458
	100 mm	01	8012-1464
Alarm output, zero- voltage	for temperature (±2 °C) and humidity (±5 % RH), accessible via 6-pin DIN socket (max. 24 V - 2.5 A), with audible signal that can be switched off	-	8012-1678
Analog output 4-20 mA	for temperature and humidity values (output not adjustable)	-	8012-1681
Calibration certificate, expanded	for temperature and humidity; for extending the measurement in center of chamber to include another test value	-	8012-1191

\* Notes > See last page



Data Sheet Model KMF 720

# BINDER

Description	*	ArtNo.
temperature measurement incl. certificate and 27 measuring points at specified temperature	-	8012-1606
temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	-	8012-1586
temperature measurement incl. certificate, 9 measuring points at specified temperature	-	8012-1565
Measurement in center of chamber at 25 °C / 60% RH or at specified test values	-	8012-1185
temperature (according to DIN12880) and humidity measurement incl. certificate, 27 temperature measuring points and 1 humidity measuring point, at 25 °C / 60 % RH or at specified values	-	8012-1612
with visual alarm (DIN 12880)	-	8012-1675
lockable door handle	-	8012-1727
including 2 reinforced racks	-	8012-0675
additional flexible Pt 100, interior, for displaying the temperature on the unit display	-	8012-1682
Additional serial interface can be used parallel to Ethernet, for Multi Management Software APT-COM™	-	8012-1712
positioned at bottom level, max. load 45 kg, with additional attachment for operation of shaking device, stirring device or roller bottle system	_	8012-1493
	temperature measurement incl. certificate and 27 measuring points at specified temperature temperature measurement incl. certificate, 15- 18 measuring points at specified temperature temperature measurement incl. certificate, 9 measuring points at specified temperature Measurement in center of chamber at 25 °C / 60% RH or at specified test values temperature (according to DIN12880) and humidity measurement incl. certificate, 27 temperature measuring points and 1 humidity measuring point, at 25 °C / 60 % RH or at specified values with visual alarm (DIN 12880) lockable door handle including 2 reinforced racks additional flexible Pt 100, interior, for displaying the temperature on the unit display Additional serial interface can be used parallel to Ethernet, for Multi Management Software APT-COM <sup>™</sup> positioned at bottom level, max. load 45 kg, with additional attachment for operation of shaking device, stirring device	temperature measurement incl. certificate and 27 measuring points at specified temperature   -     temperature measurement incl. certificate, 15- 18 measuring points at specified temperature   -     temperature measurement incl. certificate, 9 measuring points at specified temperature   -     Measurement in center of chamber at 25 °C / 60% RH or at specified test values   -     temperature (according to DIN12880) and humidity measurement incl. certificate, 27 temperature measuring points at a 1 humidity measuring point, at 25 °C / 60 % RH or at specified values   -     with visual alarm (DIN 12880)   -   -     lockable door handle   -   -     including 2 reinforced racks   -   -     additional flexible Pt 100, interior, for displaying the temperature on the unit display   -     positioned at bottom level, max. load 45 kg, with additional attachment for operation of shaking device, stirring device   -

\* Notes › See last page

### ACCESSORIES

Designation	Description	*	ArtNo.
APT-COM™ 4 GLP- Edition	for working under GLP-compliant conditions. Measured values are documented in a tamper-proof way in line with the requirements of FDA Regulation 21 CFR 11.	·	
	version 4, GLP edition	-	9053-004
APT-COM™ 4	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.		
PROFESSIONAL-Edition	version 4, PROFESSIONAL edition	-	9053-004
BINDER PURE AQUA SERVICE	System for preparation or complete desalination of tap water, complete set containing PURE AQUA 300 single-use cartridge, measuring device, and all necessary connecting parts	-	8012-0759
BINDER PURE AQUA SERVICE, accessories	Single-use, replacement cartridge for BINDER PURE AQUA System	-	6011-0165
	Basic set consisting of 2 pieces, attachment material, control unit for max. 4 light strips, 100-240 V, 50/60 Hz		
	Basic set 300, length 30 cm	-	8012-1107
LED light bars	Basic set 500, length 50 cm	-	8012-1108
	Basic set 900, length 90 cm	-	8012-1109
	Expansion set consisting of 2 pieces, attachment material: clips. For expanding the basic set of light bars		
	Expansion set 300, length 30 cm	-	8012-1716
	Expansion set 500, length 50 cm	-	8012-1717
	Expansion set 900, length 90 cm	-	8012-1718
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-001
	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature and humidity values		
pH-neutral detergent Qualification documents	Digital in PDF format	-	7057-000
	Hard copy inside folder	-	7007-000
Qualincation documents	IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature and humidity values		
	Digital in PDF format	-	7057-000
	Hard copy inside folder	-	7007-000
Rack	stainless steel	-	8012-205
Rack accessories	fasteners (1 set of 4) for additional security of racks	-	8012-062
Rack, reinforced	stainless steel, with fasteners (1 set of 4)	-	8012-067
	RS 422 cable set and RS 485 / RS 422 interface converter for connection to 10-way plug distributor		
RS 485 / RS 422 nterface converter	115 V option model	-	8012-059
interface converter	230 V option model	-	8012-058
Shelf, perforated	Stainless steel	_	8009-048

# BINDER

Designation	Description	*	ArtNo.
	consisting of fresh- and waste-water containers (20 liters each), cabling and pump		
Water supply set	external, for hanging from the back of the device	-	8012-0643
	external, free-standing	-	8012-1846
WLAN kit	The kit contains a client bridge that establishes a wireless connection between BINDER units and APT-COM4, LIMS, or customer-specific software via an Ethernet interface. It provides an alternative solution in situations where units need to be positioned in locations without an on-site Ethernet connection. In secured networks, installation and configuration must be performed by the customer's IT service.	_	8500-0164

\* Notes > See last page

### SERVICES

Designation	Description	*	ArtNo.
nstallation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	05	DL10-0300
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0700
Maintenance contracts			
Maintenance services			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	05	DL20-0710
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one temperature/humidity value, including certificate	05	DL20-092
Maintenance	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	05	DL20-040
SILVER 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	05	DL20-082
Calibration services			
Temperature and humidity calibration	Expansion –Temperature and humidity calibration with 1 measuring point in center of chamber with 1 specified pair of values, including certificate	03, 04, 05	DL30-030
	Temperature and humidity calibration with 1 measuring point in center of chamber with 1 specified pair of values, including certificate	03, 04, 05	DL30-030
Temperature and humidity measurement according to DIN12880	Temperature measurement in accordance with DIN 12880 with 27 temperature measuring points and 1 humidity measuring point in center of chamber with a pair of values specified by the user, including certificate	03, 04, 05	DL30-042
Femperature and humidity measurement, 18-1 measuring points	Temperature measurement with 18 temperature measuring points and 1 humidity measuring point in center of chamber with a pair of values specified by the user, including certificate	03, 04, 05	DL30-031
Femperature and humidity measurement, 27-1 measuring points	Temperature measurement with 27 temperature measuring points and 1 humidity measuring point in center of chamber with a pair of values specified by the user, including certificate	03, 04, 05	DL30-032
Temperature and humidity measurement, 9-1 measuring points	Temperature measurement with 9 temperature measuring points and 1 humidity measuring point in center of chamber with a pair of values specified by the user, including certificate	03, 04, 05	DL30-030
Validation services			
Validation services Execution of IQ/OQ	Execution of IQ/OQ in accordance with qualification folder	05	DL42-030
	Execution of IQ/OQ in accordance with qualification folder Execution of IQ/OQ/PQ in accordance with qualification folder	05 05	DL42-030 DL44-050
Execution of IQ/OQ		-	

\* Notes > See last page



### NOTES

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. UL mark is not granted when this option is used. 01
- 02
- Sensor calibration is performed in an accredited calibration laboratory. 03
- Calibration is performed according to the BINDER factory standard. 04
- 05 Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

### **BINDER GmbH**

Tuttlingen, Germany TEL +49 7462 2005 0 FAX +49 7462 2005 100 info@binder-world.com www.binder-world.com

### BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 FAX +852 39070507 asia@binder-world.com www.binder-world.com

#### **BINDER Environmental Testing**

Equipment (Shanghai) Co., Ltd. Shanghai, P.R. China TEL +86 21 685 808 25 FAX +86 21 685 808 29 china@binder-world.com www.binder-world.com

### **Representative Office for CIS**

Moscow, Russia TEL +7 495 988 15 16 FAX +7 495 988 15 17 russia@binder-world.com www.binder-world.com

#### **BINDER Inc.**

Bohemia, NY, USA TEL +1 631 224 4340 FAX +1 631 224 4354 usa@binder-world.com www.binder-world.us