

# Q-Sense Consumables Catalogue

- Q-Sense E<sub>4</sub> Auto
- Q-Sense E<sub>4</sub>
- Q-Sense E<sub>1</sub>
- Q-Sense D<sub>300</sub>

January 2010



QCS 001  
O-rings, standard, Viton®, 11.1x1.6 mm, 4 pcs

QFM 401  
QEC 401


QCS 002  
O-rings, standard, Viton®, 11.1x1.6 mm, 20 pcs



QCS 019  
O-rings, standard, Viton®, 12x1 mm, 4 pcs

QEM 401  
QHM 401  
QOM 401  
QWM 401  
QELM 401

QCS 023  
O-rings, highly resistant, Kalrez®, 12x1 mm, 4 pcs



QCS 017  
O-rings, highly resistant, Kalrez®, 11.1x1.6 mm, 4 pcs


QFM 401  
QEC 401




QCS 024  
Electrochem. module o-ring kit, Viton®:

QEM 401

- 12x1 mm, 2 pcs
- 1.78x1 mm, 2 pcs
- 1.15x1 mm, 4 pcs





QCS 011

Sealing gaskets, standard, Viton®,  
4 pcs

QFM 401

QCS 018

Sealing gaskets, highly resistant,  
Kalrez®, 4 pcs



QCS 027

Ellipsometry module sealing kit,  
Viton®:

- Sealing gasket, 1 piece
- 12x1 mm o-ring, 1 piece
- 14x1 mm o-ring, 1 piece
- 5x1 mm o-ring, 2 pcs
- 1.15x1 mm o-ring, 4 pcs

QELM 401



QLH 401


Complete Liquid Handling Set:

- O-rings, Viton®, 4 pcs (QFM 401 only)
- Sealing gaskets, Viton®, 4 pcs (QFM 401 only)
- Teflon® tubing, ID 0.75 mm, 5 m
- Ferrules, 24 pcs
- Nuts, 12 pcs
- Perifits, 4 pcs

E4 Auto system

E4 system

E1 system





QCS 005  
Tubing, standard for E4 and E1,  
Teflon®, ID 0.75 mm, 10 m

E4 Auto system  
E4 system  
E1 system



QCS 028  
Tubing, standard for E4 Auto,  
FEP®, ID 0.5 mm, 8 m

E4 Auto system

For probe-to-flow module connection.



QCS 006  
Pump tubing with 3 stoppers (green  
and orange), Tygon, 12 pcs

Ismatec:  
Reglo Analog  
Reglo Digital


QCS 030  
Pump tubing with 2 stoppers, Tygon  
MHSL, 6 pcs



QCS 007  
Pump tubing with 2 stoppers (black  
and orange), Tygon, 12 pcs

Ismatec:  
IPC-N4

QCS 031  
Pump tubing with 2 stoppers, Tygon  
MHSL, 6 pcs





QCS 013

Nuts, tubing holder screw, 12 pcs

Fits tubing QCS 005 and QCS 028.

QFM 401

QEC 401

QEM 401

QHM 401

QWM 401

QELM 401



QCS 012

Ferrules, for connection to nuts,  
Teflon, 30 pcs

Fits tubing QCS 005 and QCS 028.

QFM 401


QEC 401

QEM 401

QHM 401

QWM 401

QELM 401



QCS 014

Perifits, for connection between  
Teflon® tubing and Tygon pump  
tubing, 4 pcs

Fits nut QCS 013.

Ismatec:

Reglo Analog

Reglo Digital


IPC-N4



QCS 021

Plastic syringes for pump


Univentor 864 QS






QCS 020  
Quartz glass window for Window  
Module

QWM 401



QCS 029  
Optical window, 1/4 wave BK7, for  
Ellipsometry Module

QELM 401




QCS 025  
GORE® membrane for Humidity  
Module, 12.5x21.5 mm, 2 pcs

QHM 401



QCS 026  
Reference electrode plastic screw,  
for Electrochemistry Module

QEM 401





QCS 008  
Tubing, standard, Viton®, 2 m equal  
to 4 replacements

AFC 302



QCS 009  
Tubing, highly resistant, Tygon MH  
2075, 2 m, equal to 4 replacements

AFC 302




QCS 010  
Tubing, minimized volumes, Tygon  
R-3607, with connectors

AFC 302



QCS 003  
O-rings, standard, Viton®,  
4 large 11.1x1.6 mm + 4 small  
8.1x1.6 mm

AFC 302





QCS 004  
O-rings, highly resistant, Kalrez®/  
Chemraz®, 1 large 11.1x1.6 mm +  
1 small 7.7 x 1.8 mm

AFC 302



QCS 015  
Luer fittings, 3 pcs

AFC 301



QCS 016  
Valve fittings for valve QSP 002,  
3 pcs

AFC 302



QSP 002  
3-way valve

AFC 302

